



Parker Hannifin Corporation
Instrumentation Products Division
1005 A Cleaner Way
Huntsville, AL 35805 USA
Phone: +1 (256) 881-2040
Fax: +1 (256) 881-5072
Email: c-parker@parker.com
Website: www.parker.com

ITEM # CTX12, MEDIUM PRESSURE TEE FITTINGS


All Autoclave valves and fittings are supplied complete with appropriate glands and collars. To order these components separately, use order numbers listed. When using plug, collar is not required.

To ensure proper fit use Autoclave Engineers tubing.

All dimensions for reference only and subject to change. For prompt service, Autoclave stocks select products. Consult your local representative.

All general terms and conditions of sale, including limitations of our liability, apply to all

[+ more](#)



Specifications	
Connection Type	SF750CX
Outside Diameter Tube	19.05 mm 3/4 in
Pressure Rating	20000 psi 1378.93 bar
Minimum Opening	0.516 in 13.11 mm

A - Height	2.25 in 57.15 mm
B - Width	3.00 in 76.20 mm
C - Height	0.62 in 15.75 mm
D - Typical Hex	1.19 in 30.23 mm
E - Length	1.50 in 38.10 mm
F - Length	1.50 in 38.10 mm
Block Thickness	1.38 in 34.93 mm
Tubing Engagement Depth	1.00 in 25.4 mm